



High Definition Core Aligning fusion splicer

TYPE-82C




Useful cloud hosted splicer services via your smartphone App.



Advanced, Adept, Assured

Splicing 5s / Heating 9s
Splicing loss SMF 0.01dB (Typical)



High speed dual independent ovens for productivity



Touch optimised user interface and high resolution display



Proven field toughness



Long life battery for 300 splice & heat cycles

Specifications

Items	TYPE-82C	
Optical fiber requirements	Material	Silica glass
	Fiber count / Profile types	Single / SMF(G.652), MMF(G.651), DSF(G.653), NZDSF(G.655), BIF(G.657), CSF(G.654), EDF
	Fiber diameter	Cladding diameter : 80 - 150μm, Coating diameter : 100 - 1,000μm
Standard performance	Cleave length	5 - 16mm with coating clamp
	Splice loss (typical)*1	SMF : 0.01dB, MMF : 0.01dB, DSF : 0.03dB, NZDSF : 0.03dB
	Return loss (typical)	60dB or greater
	Splice time (typical)	5sec(SM G652 Quick Mode), 7sec(SM G652 Std. Mode), 7sec(Auto Mode)
	Heating time (typical)	9sec (FPS-61-2.6 sleeve, S60mm 0.25 Quick Mode)
	Splice & Heat cycles per battery full charge*2	Approx. 300 (BU-16)
	Fiber view & magnification	2 CMOS cameras observation, 380X (zoom : 760X) for X or Y single axis view, 270X for both X & Y dual axis view
Programs	Proof test	1.96 - 2.09N
	Applicable protection sleeve	60mm, 40mm & Sumitomo Nano sleeves
	Splice programs	Max. 300, 74 are pre-optimised, 226 editable by user
Functions	Heating programs	Max. 100, 27 are pre-optimised, 73 editable by user
	Splice image capture / Splice data storage	200 images / 10,000 splice data (internal memory only) 50,200/20,000 (with 8GB SD card)
	Attenuation splicing	0.1dB to 15dB in 0.1dB increments
	Universal clamps	Provided, 250μm, 900μm tight & loose buffer fiber
	Reversible coating clamps	Provided
	Dual automatic independent ovens	Provided
	User-selectable oven clamp operation	Provided
	Onboard user training video	Provided
	Automatic fiber identification	SMF / MMF / DSF / NZDSF / BIF / Other
	Automatic arc calibration	Automatically compensates for environmental condition changes
Size / Weight	Display of remaining Splice & Heat cycles	Provided (Battery mode)
	Wireless LAN connectivity (Option)*3	Provided
	Size	128(W) x 154(D) x 130(H) mm (without anti-shock rubber)
Terminals	Weight	1.9kg (without Battery) / 2.2kg (with Battery BU-16)
	Monitor	5.0" touch screen color LCD display
	DC output	DC 12V (for JR-6)
Power supply	USB port	USB 2.0 (mini-B type)
	Storage media	SD / SDHC memory card MAX32GB
	AC input	AC 100 - 240V, 50/60Hz (ADC-16)
Operating condition	DC input	DC 10 - 15V
	Battery pack	Li-ion 10.8V, 6,400mAh (BU-16)
Storage condition	Altitude : 0 - 6,000m, Temperature : -10 - +50°C, Humidity : 0 - 95% (non-condensing), Wind velocity : up to 15m/sec	
Electrode life *4	Temperature : -40 - +80°C, Humidity : 0 - 95% (non-condensing), Battery : -20 - +30°C (long term)	
Software updates	6,000 arc discharges	
Data management	Internet	
	Can be stored, edited and analyzed by dedicated PC software	

*1 : Average value of the final inspection in room temperature with Sumitomo identical fiber. Measured by cut-back method relevant to ITU-T and IEC standards.

*2 : Splice & Heat cycles may vary depending on the battery status and the operating environment.

*3 : Wireless LAN connectivity is not available in all countries. For more details, please refer to our Web site. <http://global-sei.com/sumitomo-electric-splicers/>

*4 : Achieved in lab condition. Electrode life may vary depending on the operating environment.

Environmental Durability*

Test details	Test details
Shock resistance	Drop from 76cm on 5 faces (excluding top face)
Impact resistance	Equivalent to IK07 on LCD monitor (Protected against 2J impact, it is equivalent to a 500g force from 40cm)
Water resistance	Equivalent to IPX2 (Operates normally after being exposed to water dripping at 3mm/min. for at least 2.5 min on each of 4 surfaces tilted at 15°)
Dust resistance	Equivalent to IP5X (Operates normally after 8 hours in a test chamber with circulating dust particles smaller than 75 μm)

*Splicer operation after shock, impact, water or dust tests, was confirmed under battery power, by Sumitomo.
Does not guarantee the product will not be damaged by these conditions.

Basic Accessories

Part name	Part No.	Qty.
AC adapter	ADC-16	1 pc
AC power cord	PC-AC<X>*	1 pc
Cooling tray	—	1 pc
Spare electrode	ER-10	1 pair
Quick reference guide	—	1 pc
Carrying case with worktable	CC-82	1 pc
Hand strap	—	1 pc
USB cable	—	1 pc

*X=2(USA), 3(EU), 4(JP), 5(UK/HK), 8(CHINA), 9(INDIA), 10(BRAZIL)
Items listed in Basic Accessories are always included with the splicer body. Overall kit content may vary regionally. Please check with your local authorised reseller to confirm kit content in your region.



Carrying case with worktable
CC-82




Handy cleaver
FC-8R series



Table-top cleaver
FC-6 / FC-6R series



Jacket remover
JR-M03



Available for
Lynx-Custom Fit™
Splice-On Connector



Electrode
ER-10

Accessories

Part name	Part No.	Remarks	
Accessories for Splicer	Wireless LAN SD card	WLS-0308 For SumiCloud™ connection	
	Fiber holder	FHS-025	For φ0.25mm single fiber
		FHS-09	For φ0.9mm single fiber
		FHS-025/LB5	For 0.9mm loose buffered single fiber
		FHD-1	For drop/indoor cable (Cable size : typical 2.0 x 3.1 or 2.6mm)
	Battery pack	1SM-ST	For indoor cable (Cable size : typical 1.6 x 2.0mm)
		FHC-3	For 3mm cable
		BU-16	Li-ion 6,400mAh
	Battery charger	BC-16	—
	Car battery cable	PCV-16	For car battery operation (cigarette socket type)
V-groove cleaning brush	VGT-2	Brush for cleaning V-groove	
Electrode	ER-10	—	
Accessories	Handheld fiber cleaver	FC-8R-FC Automatic blade rotation cleaver with cleave counter	
		FC-8R-F Automatic blade rotation cleaver	
	Fiber cleaver	FC-6S-C Table-top high precision cleaver	
		FC-6RS-C Automatic blade rotation cleaver	
	Jacket remover	JR-M03 Jacket remover for single fiber	
	Loose tube cutter	LTC-01 —	
	Alcohol dispenser	HR-3 —	
	Fiber protection sleeve	FPS-1	60mm, diameter after shrink approx. φ3.2mm
FPS-40		40mm, diameter after shrink approx. φ3.2mm	
FPS-61-2.6		61mm, diameter after shrink approx. φ2.6mm	

SUMITOMO ELECTRIC INDUSTRIES, LTD.

Tokyo (Japan)

Sumitomo Electric Industries, Ltd.

Akasaka Center Building, 1-3-13, Motoakasaka,
Minato-ku, Tokyo, 107-8468, JAPAN

TEL: +81-3-6406-2666

<http://global-sei.com/sumitomo-electric-splicers/>

Gurgaon (India)

SEI Trading India Pvt. Ltd.

802, Vatika City Point, M.G. Road,
Gurgaon 122002, Haryana, India

TEL: +91-124-4577470

<http://www.sumitomosplacers.in/>

Candid Optronix Pvt Ltd

A-129/2, Nirankri Colony, Delhi-9 (India)

TEL: +91-11-2704-4633, 2760-3010

Email: sales@optronix.in

<https://www.optronix.in>